


The first name in sample
preparation equipment



K LOX PROOFER



Above: The Automatic K Lox.
Below: The Hand K Lox.



The simplest method of applying flexo inks and other fluid coatings onto any substrate to produce accurate and repeatable proofs that closely resemble conventional flexo printing. The K Lox Proofer is an essential tool for ink makers and printers alike. Ideal for quality control and presentation samples, R&D and computer colour matching data.

MAIN FEATURES


- Instant flexo proofs.
- Easy to use – easy to clean.
- Excellent repeatability.
- Reduces press down-time.
- Fully interchangeable rollers up to 500 screen.
- Hand and automatic versions available.

The first name in sample preparation equipment

K LOX PROOFER

K Lox

A bead of ink is placed between an engraved anilox roller and a rubber roller as illustrated below. It is essential to have constant pressure between the rollers for consistent prints and this is ensured by two weights. When the K Lox is drawn smoothly over the substrate an accurate film of ink is printed producing a sample up to 4.5" (115mm) wide. After removing the weights, both rollers are easily cleaned. Anilox rollers with screens for solid, line and half-tone printing may be selected as required.




Hand K Lox

The Hand K Lox provides a cost effective and simple means of proofing flexo inks. It is available as a single unit or may be ordered as a comprehensive system. The Hand K Lox system comes complete with 3 standard engraved anilox rollers, 2 rubber rollers and a cleaning storage rack.

Automatic K Lox

With a little practise, the K Lox user is able to produce consistent results with the hand unit. However, where a number of operators may be involved or when the highest degree of repeatability is demanded (e.g. when using the prints for computer colour matching), the Automatic K Lox is recommended. This machine eliminates any variation in speed and pressure and an accurate print is produced every time. The unit operates at variable speeds up to 15m/min. An air driven version is available for use in hazardous areas.



Above: Cleaning/storage rack.

Accessories

Cleaning/storage rack for up to 6 rollers.

Wide shouldered rubber roller (for use on slippery substrates e.g. polythene).

Standard Rollers

TYPE	SCREEN		CELL VOLUME	
	CELLS / LINEAR INCH	CELLS / LINEAR CM	CBM	CM ³ /M ²
400/5	400	160	2.8	4.3
200/12	200	80	6.6	10.2
180/14	180	70	10.7	16.6
140/10	140	55	13.0	20.2
100/18	100	40	25.2	39.1

Other screens and wire wound rollers can be manufactured to customer specification.



RK PrintCoat Instruments Ltd.,

Litlington, Royston, Herts SG8 0QZ United Kingdom

Tel: +44 (0)1763 852187 Fax: +44 (0)1763 852502

E-mail: sales@rkprint.com

www.rkprint.com